



Kick & Click[™]

Easy office desk assembly

Easy and intuitive desk assembly with Kick & Click™


Kick – Click – Done

Kick & Click™ is the innovative top frame for office desks. It is an easy and intuitive way to mount the columns to the tabletop.

Simply mount the different parts, “kick” them together and it says “click”. This means no screws and no tools for mounting.









Watch the assembly video
[LINAK.COM/KICKANDCLICK](https://linak.com/kickandclick)




- ✓ No tools
- ✓ No screws
- ✓ Intuitive assembly

Quick assembly - no screws or tools needed



Click!



One solution - available in three versions

Kick & Click™ is available in three versions so you can find the solution that best fits you and your desk design.

Kick & Click™ Adjustable

- Solution for various designs
- Telescopic design for desks ranging from
- 1.40 m - 2.0 m width
- Compatible with Kick & Click™ 3rd leg kit

Kick & Click™ Fixed

- Compact solution for small desks with width of 1,20 m
- Ideal for e.g. touchdown and multi-user desks
- Compatible with Kick & Click™ 3rd leg kit for 3-leg office desks


Kick & Click™ Base

- Independent and flexible desk width
- For desks where stability is achieved via the tabletop
- For desk designs with customised rails


Optional, Kick & Click™ can also be used for creating 3-leg office desks by joining a Kick & Click™ 3rd leg kit with a Kick & Click™ system.

Choose between T-Desk or C-Desk design

The flexible position of the cantilever enables T-Desk or C-Desk designs. Simply place the columns either centrally or off-centre. Pre-marked positions on the cantilever guides you easily through the assembly. Of course, this counts for all three Kick & Click™ versions.




T-Desk with columns placed centrally.




C-Desk with columns placed off-centre.


Kick & Click™ Fixed



Kick & Click™ Adjustable



Kick & Click™ Base



Freedom to design

With Kick & Click™ there are no limitations. It is one solution, but it gives you various design options. We give you freedom to design, because we know that great products enable great design.

Lifting columns available with Kick & Click™



DL5 

Speed: 38 mm/sec.
Max thrust: 800 N/leg
Stroke length: 500 mm
Built-in dim: 645 mm



DL6 

Speed: 38 mm/sec.
Max thrust: 800 N/leg
Stroke length: 650 mm
Built-in dim: 560 mm



DL8

Speed: 38 mm/sec.
Max thrust: 800 N/leg
Stroke length: 500 mm
Built-in dim: 645 mm



DL9

Speed: 38 mm/sec.
Max thrust: 800 N/leg
Stroke length: 650 mm
Built-in dim: 560 mm



DL10 

Speed: 38 mm/sec.
Max thrust: 800 N/leg
Stroke length: 500 mm
Built-in dim: 645 mm



DL11 

Speed: 38 mm/sec.
Max thrust: 800 N/leg
Stroke length: 650 mm
Built-in dim: 560 mm



DL15 

Speed: 38 mm/sec.
Max thrust: 800 N/leg
Stroke length: 500 mm
Built-in dim: 645 mm



DL16 

Speed: 38 mm/sec.
Max thrust: 800 N/leg
Stroke length: 650 mm
Built-in dim: 560 mm



DL19 

Speed: 38 mm/sec.
Max thrust: 800 N/leg
Stroke length: 650 mm
Built-in dim: 560 mm

Desk Frame 1



LINAK® has made it easy for you to build your unique desk. With everything Plug & Play™, we made the concept 'Desk Frame 1' for offering you an easy complete package of everything you need to create your own unique electric adjustable sit-stand desk. Just combine the three boxes: DL SetPack (including lifting columns, desk panel, control box and cables), Kick & Click™ top frame and DL Feet. All you need is to add your own tabletop.



DL SetPack

Choose selected DESKLINE® products as a pre-packed box, containing two lifting columns, a desk panel, a control box, and the necessary cables. Enjoy great flexibility choosing between different column profile designs (rectangular, square, or round) and several Desk Panel types.



Kick & Click™

Add the innovative Kick & Click™ top frame for office desks with two or three legs. It fits with all motor housing columns and for the design of T- and C-desks.



DL Feet

DL Feet are a perfect match for LINAK lifting columns. 10 variants for stable T-Desk designs give you the maximal design freedom. Available in two different lengths (560 mm or 710 mm) and two mounting styles (on top or recessed).





For further information about the DESKLINE® product programme:
LINAK.COM/DESKLINE



For more information please visit our website:
LINAK.COM/KICKANDCLICK



Global presence

LINAK has a well-developed sales and service organisation in Europe, the Americas, Asia and Australia. Therefore, we can assist you and your customers locally, under the global sales concept idea: Be global, act local

TERMS OF USE

The user is responsible for determining the suitability of LINAK products for a specific application. LINAK takes great care in providing accurate and up-to-date information on its products. However, due to continuous development in order to improve its products, LINAK products are subject to frequent modifications and changes without prior notice. Therefore, LINAK cannot guarantee the correct and actual status of said information on its products. While LINAK uses its best efforts to fulfil orders, LINAK cannot, for the same reasons as mentioned above, guarantee the availability of any particular product. Therefore, LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or other written material drawn up by LINAK.

All sales are subject to the Standard Terms of Sale and Delivery for LINAK. For a copy hereof, please contact LINAK.

LINAK has a world-class sales and service organisation.
Today we are present in 35 countries all over the world.
For further information, please visit our website: **LINAK.COM**