



Battery charger CH01 - 2nd generation

Data sheet

Battery charger CH01 - 2nd generation

The CH01 Battery Charger gives the possibility to interchange the plug type with a simple slide-on operation.

This gives great versatility and a logistical advantage reducing stocks and costs.



Features:

- Mains voltage: 100-240 VAC/50-60 Hz
Switch Mode Power Supply (SMPS)
- Mains cable: 2000 mm with straight DC-plug (5.5 x 2.5)
- Charging voltage: 28 V + 0.3 V/ -0.6 V
- Charging current: Max. 500 mA
- Colour: Black RAL 9005
- LED indication: Green LED for power on
Yellow LED for charging

Usage:

- Usage temperature: +5 °C to 40 °C
- Storage temperature: -10 °C to 50 °C
- Relative humidity: 20% to 80% - non-condensing
- Atmospheric pressure: 700 to 1060 hPa
- Height above sea level: Max. 3000 meters
- Power consumption: < 0.5 W
- Approvals: IEC 60601-1
PSE

Plug types



Charging module



English plug



Australian plug



Euro plug



Korean plug



US plug



Japanese plug

Charger CH01	
Description	Part number:
Charging module (straight plug)	CH01-01
English plug	CH01UK-01
Australian plug	CH01AUS-01
Euro plug	CH01EU-01
Korean plug	CH01KC-01
US plug	CH01US-01
Japanese plug	CH01JP-01

Please order charging module in multiples of 70 as there are 70 pieces in a box.

LINAK® accepts no responsibility for possible errors or inaccuracies in catalogues, brochures, and other material. LINAK reserves the right to change its products without prior notice. LINAK cannot guarantee product availability and reserves the right to discontinue the sale of any product. The user is responsible for determining the suitability of LINAK products for a specific application. All sales are subject to the 'Standard Terms of Sale and Delivery', available on LINAK websites.

LINAK and the LINAK logotype are registered trademarks of LINAK A/S. All rights reserved.