



Charger CHL40

Data sheet

CHL40

The CHL40 charger is an important part of the LIFT40 family. It functions as a wall charger when mounted on the wall, but also as a more mobile charger simply placed horizontally on its back on any surface.

The CHL40 is provided with very visible charging indicators and powered by the CH01 wall charger equipped with universal power input for worldwide use.



Features and Options:

- Functional and elegant design with ergonomic battery handling
- Charging time BAL40 battery pack: Approx. 5-6 hours
- Charging current: Up to 500 mA (from CH01)
- Connection charger: DC plug for connecting the CH01
- Charging indicator: LED
- Colour: Light grey RAL 7035
- Protection class: IPX4

Usage:

- Usage temperature: +5 °C to 40 °C
- Storage temperature: -10 °C to 50 °C
- Relative humidity: 20% to 80% - non-condensing
- Atmospheric pressure: 700 to 1060 hPa
- Height above sea level: Max. 3000 meters
- Nominal current draw: Max. 500 mA (CH01 spec)
- Power consumption (standby): Max. 2.5 W
- Power consumption (charging): Max. 19 W
- Approvals: (pending)
 - IEC 60601-1
 - ANSI/AAMI ES60601-1
 - CAN/CSA-22.2 No. 60601-1
 - Australian deviation, Canadian deviation

LINAK® accepts no responsibility for possible errors or inaccuracies in catalogues, brochures, and other material. LINAK reserves the right to change its products without prior notice. LINAK cannot guarantee product availability and reserves the right to discontinue the sale of any product. The user is responsible for determining the suitability of LINAK products for a specific application. All sales are subject to the 'Standard Terms of Sale and Delivery', available on LINAK websites.

LINAK and the LINAK logotype are registered trademarks of LINAK A/S. All rights reserved.