



Hand Control HC40 TWIST™ Standard Data sheet

HC40 TWIST™ Standard

The Hand Control HC40 TWIST™ Standard for the operation of electric adjustable beds is designed to match modern bedroom interior. The HC40 TWIST™ sets a new standard within hand control design and even a basic bed system can now be created with a well-designed hand control. It is designed for a basic bed system with back and leg adjustment up/down as well as simultaneous drive.

The HC40 TWIST™ fits ergonomically well in the hands of both right-handers and left-handers. Hold it and you will experience how natural and relaxed the position of your hand is when controlling the bed. Reference lines on the back and concave and convex buttons on the front ensure one-grip-reach-all-buttons and an easy orientation of the remote.

The HC40 TWIST™ is developed for easy customisation. Customise the colour or surface and make a unique offering for a specific brand or bed series.



Features:

- Unique design
- Ergonomically good to hold in the hand
- Control two references (Back and leg as standard)
- Simultaneous drive up and down
- Plastic parts black RAL 9005
- Two AAA changeable batteries (not included)
- Backlight in buttons
- Button for Under Bed Light
- Delivered in a fabric bag
- PVC-Free™

Options:

- Customise print on keypad
- Customise logo on battery cover
- Customise top cover and battery cover colour
- Enable child lock
- Accessory: Stand to place the HC40 on the bed side table


Usage:

- Compatible with the LA18 IC Standard, TD4 Standard, TD5 Standard and the Bluetooth® Adapter.
- Battery life at normal use of 1 minute per day is approximately 7 years
- Complies with FCC and IC
- Complies with UL 962, EN 62368-1, KC and RCM
- Operational temperature: 5 to 40°C
- Stock temperature: -10 to +50°C




Do **not** expose to direct sunlight.

Dimension drawing




**Accessory
HC40STAND001**




An accessory to give the HC40 TWIST™ a base on the bed side table.
Colour: Black RAL9005.
Item number: HC40STAND001

Dimension drawing



HC40 TWIST™ Standard

Ordering example:



The HC40 TWIST™ Standard comes in boxes of 79 pieces and must be ordered in quantity divisible by 79.

The two AAA batteries are not included and must be ordered separately. The article number (bag with two AAA batteries) is: 0063023.

The HC40 stand is an accessory and must be ordered separately. The article number is HC40STAND001.

Terms of use

The user is responsible for determining the suitability of LINAK products for specific application. LINAK takes great care in providing accurate and up-to-date information on its products.

However, due to continuous development in order to improve its products, LINAK products are subject to frequent modifications and changes without prior notice. Therefore, LINAK cannot guarantee the correct and actual status of said information on its products.

While LINAK uses its best efforts to fulfill orders, LINAK cannot, for the same reasons as mentioned above, guarantee the availability of any particular product. Therefore, LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or other written material drawn up by LINAK.

All sales are subject to the Standard Terms of Sale and Delivery for LINAK. For a copy hereof, please contact LINAK.