



Hand Control HD80 Data sheet

HD80

The HD80 makes it possible to have two hand controls in one unit. The hand control is equipped with a magnet locking function, making it possible to have two levels of operation – one for the patient and relatives and one for the caregiver staff. The HD80 provides a great overview using LED indication of functions being locked or unlocked. The hand control is designed to work with OpenBus™ systems.

With the HD80, you get:

- Up to 6 rows of buttons with optional LED indication
- Up to 42 LEDs for indication
- LINAK OpenBus™ technology
- Intuitive operation
- 2 levels of operation: patient and caregiver level
- LED light



Features and Options:



- Housing colour: Light grey (RAL 7035)
Dark grey (RAL 7016)
- Protection class: IPX4 (standard), IPX6 Washable DURA™
- Number of buttons: Up to 11 dome keys, 1 magnet key sensor
- Front cover: Standard or customised
- Cable: Coiled 600 mm PU modular plug
- Button type: Domes and magnet key sensor.
For activating the magnet key sensor use the magnet key 0858008
- LED indication: Up to 42 LEDs, option with LED light
- Attachment: Via hook or magnet

Usage:


- Usage temperature: 5 °C to 40 °C
- Storage temperature: -10 °C to +50 °C
- Compatibility: Compatible with CB6 and OpenBus™ control boxes.
Please contact LINAK.
- Relative humidity: 20% to 80% - non-condensing
- Atmospheric pressure: 700 to 1060 hPa
- Height above sea level: Max. 3000 meters
- Approvals: IEC60601-1,
ANSI/AAMI ES60601-1 and
CAN/CSA-22.2 No 60601-1

Dimensions (mm):

HD80



Hook option




Magnet option

Ordering example:

<p>H D8 4 C1 J 055 0 0 0 4 - 2 0 012 001 2 D 1 C 0 0 0</p>	<p>Not used</p> <p>Not used</p> <p>Not used</p> <p>Cable type</p> <p>Cable matr.</p> <p>Plug type</p> <p>Cable colour</p> <p>SW Configuration</p> <p>Functionality</p> <p>Mounting</p> <p>Colour</p> <p>IP-Degree</p> <p>Not used</p> <p>Not used</p> <p>Not used</p> <p>Front cover number</p> <p>Front cover</p> <p>Interface</p> <p>Number of rows</p> <p>Control type</p> <p>Controls</p>	<p>0 = None</p> <p>0 = None</p> <p>0 = None</p> <p>C = Coiled 600 mm</p> <p>1 = PU</p> <p>D = Modular Plug 10 PIN / 6-wires</p> <p>2 = Grey RAL7035 3 = Dark Grey RAL 7016</p> <p>xxx= Special Lix configuration 001= Standard software</p> <p>012 = Standard 01X = Special</p> <p>0 = Hook M = Magnetic</p> <p>2 = Grey RAL 7035 3 = Dark Grey RAL 7016</p> <p>4 = IPx4 (Standard) W = IPX6 Washable DURA™</p> <p>0 = None</p> <p>0 = None</p> <p>0 = None</p> <p>The last 3 digits in the front cover number</p> <p>J</p> <p>C1 = OpenBus™ "LIXEDIT" - Configurable CX = Special (made by software department)</p> <p>0 = None Definition: Placing of button rows used 1 = 1 row defines number of rows 2 = 2 rows 3 = 3 rows 4 = 4 rows 5 = 5 rows 6 = 6 rows</p> <p>D8 = HD8x</p> <p>H = All Hand controls</p>
--	--	--

Front covers for HD80



00HD841J-055
(standard)

Magnet key - article no. 0858008



Terms of use

The user is responsible for determining the suitability of LINAK products for specific application. LINAK takes great care in providing accurate and up-to-date information on its products.

However, due to continuous development in order to improve its products, LINAK products are subject to frequent modifications and changes without prior notice. Therefore, LINAK cannot guarantee the correct and actual status of said information on its products.

While LINAK uses its best efforts to fulfill orders, LINAK cannot, for the same reasons as mentioned above, guarantee the availability of any particular product. Therefore, LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or other written material drawn up by LINAK.

All sales are subject to the Standard Terms of Sale and Delivery for LINAK. For a copy hereof, please contact LINAK.