



DESKLIFT™ SetPack

Data sheet

DESKLIFT™ SetPack

DESKLIFT™ SetPack is a convenient way of offering a complete 2-leg motor set packed in a box. Choose between several preconfigured systems and get a ready to ship system. This solution is especially useful for onsite assembly. The box and inlay are all made of cardboard making it easy to dispose and recycle after use. The box protects the content and ensures problem-free handling. Combined with a Kick & Click™ set and a DESKLIFT™ Feet set, the DL SetPack forms a complete height adjustable office desk frame.



Products available for DESKLIFT™ SetPack:

Columns:	DL5, DL6, DL10, DL11, DL15 or DL16, DL19 standard or IC versions
Control box:	CBD6S 200W (120V & 230V) or SMPS001, SMPS2 or SMPS006 if an IC system is selected
Cables:	Motor cables: 1000 mm, 1550 mm or 2000 mm) Mains cable (country specific)
Desk panels:	DPA, DPB, DPG1K, DPG1M, DPG1B, DPG1C, DPF1K, DPF1D, DPF1M, DPF1C (+mounting bracket)

For further product information, please see combination overview.

Details about the box


- Neutral, brown cardboard box
- Made of recyclable material. The box and inlay feature the "recycle mark"
- Dimensions:
DL5/DL6 box: 230x785x140 mm
DL10/DL11/DL19 box: 290x795x140 mm
- Boxes on a pallet:
DL5/DL6: 30 boxes per pallet (5 boxes in 6 layers)
DL10/DL11/DL19: 24 boxes (4 boxes in 6 layers)
- Typical weight of a box is 15 - 19 kg, depending on column type.



Please observe that DESKLIFT™ SetPack boxes are not meant for single package shipment

Combination overview:

DLS 2 DL06 0 E B 650 560 A AA 0 A AA 0 0 0



Standard
Standard
DPF bracket
Desk panel

Motor cable
DC cables
Mains cable
(* = PVC Free)

Control box
Power supply

Installation dim.
Stroke length

Bracket
Colour

Motor type
Pitch

Column type

Desk type

DESKLIFT SetPack

0 = Standard
0 = Standard
B = 90 degree
0 = None
AA = DPA
AB = DPB
AD = DPG1K
AE = DPG1M Full version
AF = DPG1M Limited version
AG = DPG1B Full version
AH = DPG1B Limited version
AI = DPG1C Full version inch
AJ = DPG1C Full version cm
AK = DPF1K
AL = DPG1C Limited version inch
AM = DPG1C Limited version cm
AN = DPF1M
AO = DPF1D cm
AP = DPF1D inch
AQ = DPF1C cm
AR = DPF1C inch
A = 1000 mm
B = 1550 mm
C = 2000 mm
0 = Standard
A = 1800 mm
B = 3500 mm
AA = EU 0015869*, 2.0m
AB = UK 0015588, 3.2m
AC = US 0015942, 3.2m
AD = CH 0015833, 3.2m
AE = EU 0015562, 3.2m
AF = CH 0015618*, 2.0m
AG = US 0015862*, 3.2m
AH = KOR 0015864, 3.2m
AI = EU 0015870*, 3.2m
AJ = JP 0015841, 3.2m
AK = EU 0015801 (SMPS006)
AL = UK 0015804 (SMPS006)
AM = JP 0015806 (SMPS006)
AN = US 0015188 (SMPS006)
AO = KOR 0015865 (SMPS006)
A0 = No cable (SMPS001/002)
A = CBD6S, 200W, EU
B = CBD6S, 200W, US
F = SMPS001
G = SMPS002
H = SMPS006
560 = 560 mm
645 = 645 mm
650 = 650 mm
500 = 500 mm
0 = No bracket
1 = Bench bracket (only DL19)
A = Grey RAL 9006
B = Black RAL 9005
D = White RAL 9016
E = PIEZO
0 = Standard
0 = Standard spindle pitch (20 mm)
1 = 12 mm spindle pitch (DL6 or DL19)
DL5 = DL5 or DL5IC
DL6 = DL6 or DL6IC
DL10 = DL10 or DL10IC
DL11 = DL11 or DL11IC
DL15 = DL15 or DL15IC
DL16 = DL16 or DL16IC
DL19 = DL19 or DL19IC
2 = 2 legs
DLS

Terms of use

The user is responsible for determining the suitability of LINAK products for specific application. LINAK takes great care in providing accurate and up-to-date information on its products.

However, due to continuous development in order to improve its products, LINAK products are subject to frequent modifications and changes without prior notice. Therefore, LINAK cannot guarantee the correct and actual status of said information on its products.

While LINAK uses its best efforts to fulfill orders, LINAK cannot, for the same reasons as mentioned above, guarantee the availability of any particular product. Therefore, LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or other written material drawn up by LINAK.

All sales are subject to the Standard Terms of Sale and Delivery for LINAK. For a copy hereof, please contact LINAK.