



Cardin RF-control Data sheet

Cardin RF-control

The Cardin RF-control is a wireless radio frequency remote control. It is a 2-channel system.

Combined with a LINAK motor control it is possible to drive an actuator up and down.



Third party product

Technical data:


Receiver:

- Supply: 12-24V 4Clubc
- Max. consumption: 6w
- Frequency: 433.92 MHz
- Working temperature: 20 to 60°C
- Capacity in open space: 50-100 m
- Protection rating: IP20

Transmitter:

- Frequency: 433.92 MHz
- Power by battery: 12 udc (6P23A)
- Working temperature: -10 to 55°C
- Dimensions: 80 x 39 x 12 mm

Dimensions:



Ordering:

Cardin RF-control 2 CH Receiver:

Cardin RF-control 2 CH Transmitter:

Ordering no.: TR-RMS435200

Ordering no.: TR-TRS435200



The specified product is produced by Cardin Elettronica S.p.A.

Specifications subject to change without prior notice.
It is the responsibility of the product user to determine the suitability of the products for a specific application. LINAK Danmark will at point of delivery replace/repair defective products covered by the warranty if promptly returned to LINAK Danmark. No liability is assumed beyond such replacement/repair.

LINAK® accepts no responsibility for possible errors or inaccuracies in catalogues, brochures, and other material. LINAK reserves the right to change its products without prior notice. LINAK cannot guarantee product availability and reserves the right to discontinue the sale of any product. The user is responsible for determining the suitability of LINAK products for a specific application. All sales are subject to the 'Standard Terms of Sale and Delivery', available on LINAK websites.

LINAK and the LINAK logotype are registered trademarks of LINAK A/S. All rights reserved.