



| Version | Combination code | B (Built-in length) [mm] | S (Stroke length) [mm] | O (Outer profile length) [mm] |
|------------------|-------------------|--------------------------|------------------------|-------------------------------|
| Standard columns | | | | |
| EU | DL11xxxx0635575 | 575 | 635 | 498 |
| PIEZO | DL11xxxxE650560 | 560 | 650 | 498 |
| BIFMA | DL11xxxx665518 | 518 | 665 | 456 |
| XL | DL11xxxx965740 | 740 | 965 | 663 |
| PLUS™ columns | | | | |
| EU | DL11xxxPx650560 | 560 | 650 | 498 |
| BIFMA | DL11xxxPx665518 | 518 | 665 | 456 |
| High-speed XL | DL113xxxPx1100785 | 785 | 1100 | 723 |

Built-in length, stroke length, and outer profile length

All rights reserved

Date:

3 October 2023

Description:

DESKLIFT™ Column DL11
Built-in dimensions / stroke lengths

LINAK® 
WE IMPROVE YOUR LIFE