



Version	Combination code	B (Built-in length) [mm]	S (Stroke length) [mm]	O (Outer profile length) [mm]
EU	DL11xxxxx650560	560	650	498

Built-in length, stroke length, and outer profile length



Motor housing

Bottom plate



Profile dimensions (mm)

All rights reserved

Date:  
3 October 2023

Description:

DESKLIFT™ Column DL11 IC

