



Version	Combination code	B (Built-in length) [mm]	S (Stroke length) [mm]	O (Outer profile length) [mm]
EU	DL18xxxxx500645	645	500	590
BIFMA	DL19xxxxx665518	518	665	456
High-speed XL	DL193xxxPx1100785	785	1100	723


Built-in length, stroke length, and outer profile length



Motor housing



Bottom plate



Profile dimensions (mm)

All rights reserved

Date:

30 June 2023

Description:

DESKLIFT™ Column DL19



WE IMPROVE YOUR LIFE