



Combination code	B (Built-in length) [mm]	S (Stroke length) [mm]	O (Outer profile length) [mm]
DL8xxxxxx500645	645	500	640


Built-in length, stroke length, and outer profile length



Motor housing



Bottom plate



Profile dimensions (mm)

All rights reserved

Date:
3 October 2023

Description:

DESKLIFT™ Column DL8

