



Dimension table

Dim	in	mm	Dim	in	mm
A	7.56 SQ	192 SQ	H	3.54	90
B	5.35	136	I	4.92 SQ	125 SQ
C	ø0.51	ø13	J	3.95	75
D	Stroke + 8.70	Stroke + 221	K	1.42	36
E	5.748 SQ	146 SQ	L	6.30	160
F	0.39	10	M	8.50	216
G	0.41	10	S	Stroke	Stroke

All rights reserved

Date:

17 June 2010

Description:

Lifting Column LC25
with 10 mm endplates (F)



WE IMPROVE YOUR LIFE