



Hand Control HB50 Data sheet

HB50

The HB50 is primarily designed for the LINAK JUMBO system and LINAK control boxes with memory functions. The HB50 gives the user access to a range of memory functions, allowing present positions to be stored. For use in a wide variety of hospital and patient care.




Features and Options:

- Hand control for up to 4 actuators
- Ergonomic and universal design
- High-strength plastic housing
- Easy-touch buttons
- Hook for easy placement
- Protection class IPX1
- 2.4 m straight cable
- Customised front cover
- Protection class IPX5
- 0.6 m coiled cable or extra long cable
- Anti-slip rubber tip for placement on a flat surface (special article)
- Colour: grey - only (RAL 7035)

Usage:

- Ambient temperature: +5° to +40°C
- HB50B is compatible with CBJ2
- HB50E is compatible with CB9P..Px types (except..PM/PN) and CB14 with memory
- HB50J is compatible with CBJ1
- HB50Y is for Jumbo Home (CBJH)

Dimensions:



Compatibility:

	CB9..Px (not ..PM/PN)	CB14	CBJ1	CBJ2	CBJH
HB50B				x	
HB50E	x	x			
HB50J			x		
HB50Y					x

HB50


Ordering example:

H B 5 1 B 00 - 02 1 0 0

- Cable:**
 - 0 = Straight, 2400 mm, 8 pole DIN plug
 - 1 = 9-core coiled, 600 mm, 8-pole DIN plug
 - 2 = 6-core coiled, 500 mm, 8-pole DIN plug only HB51B, HB52J
 - 5 = 9-core coiled with extra long straight end, 600 mm/1550 mm
 - 6 = Straight cable, 1500 mm, 8-pole modular jack
 - C = 5-wire coiled, 600 mm, 10p. modular jack for e.g. CBJH
- IP - rating:**
 - 0 = IPX1
 - 1 = IPX5
- Colour:**
 - 1 = Grey
- Front plate no.** Customer designed front cover
- Special code no. if not 00**
- Functionality:**
 - B = Jumbo (CBJ2)
 - E = for CB14M, CBD1 and CB9..Px (Not CB9..PM /..PN).
 - J = Jumbo (CBJ1)
 - Y = Jumbo Home (CBJH)
- No. of channels:** 1 - 4


Grey
 0015752
 0015762
 0015764
 0015767
 0567011
 0964040

Overview for HB5x functionality B, J, Y:



Overview for HB5x functionality E:

! The shown functions are according to CB14M matrix for more details please contact your local LINAK.



HB50 Standard front covers - when ordering check that the hand control functionality corresponds to the symbols on the front cover. The last 2 digit in the front cover code are to be used in the ordering example (XX).



HB51-000



HB51-002



HB51M-000



HB52-000



HB52-004




HB52M-000



HB53-000



HB53-003




HB53M-000




HB54-000



HB54M-000



HB51-012



HB52-019

Terms of use

The user is responsible for determining the suitability of LINAK products for specific application. LINAK takes great care in providing accurate and up-to-date information on its products.

However, due to continuous development in order to improve its products, LINAK products are subject to frequent modifications and changes without prior notice. Therefore, LINAK cannot guarantee the correct and actual status of said information on its products.

While LINAK uses its best efforts to fulfill orders, LINAK cannot, for the same reasons as mentioned above, guarantee the availability of any particular product. Therefore, LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or other written material drawn up by LINAK.

All sales are subject to the Standard Terms of Sale and Delivery for LINAK. For a copy hereof, please contact LINAK.