



# Hand Control HC40 TWIST™ Advanced Data sheet

# HC40 TWIST™ Advanced

The Hand Control HC40 TWIST™ for the operation of electric adjustable beds is designed to match modern bedroom interior with features that eliminate the need for multiple bedside devices. No matter how many motors, favourite positions and massage options the bed offers, the design of this remote control remains clean.

The HC40 TWIST™ fits ergonomically well in the hands of both right-handers and left-handers. Hold it and you will experience how natural and relaxed the position of your hand is when controlling the bed. Reference lines on the back and concave and convex buttons on the front ensure one-grip-reach-all-buttons and an easy orientation of the remote.

The control is designed for day and night use. The screen brightness adjusts to the surroundings, dimming the light at night, if the user wants to check the time. Shake it sideways twice to illuminate a torch that guides the way in the dark. Set an alarm and wake up quietly the next morning by a vibrating massage - leaving your partner undisturbed. Grab the remote to stop the alarm and get a personalised good morning greeting. Set the top row buttons to have the favourite features accessible with a single click.

The HC40 TWIST™ is developed for easy customisation. Get your own logo as the start-up screen and let your brand be the first thing, the user meets. Customise the colour or surface and make a unique offering for a specific brand or bed series.



## Features:

- Unique design
- Control up to four references (back, leg, foot and neck as standard)
- Save up to four favourite positions
- Control up to two massage references (back and leg as standard)
- Three shortcut buttons: save the most used functionalities to be only one click away
- Time & day displays by movement of the hand control
- Alarms: set up to three alarms and massage motors work as a wake-up
- Simultaneous drive down
- Button for Under Bed Light
- Torch; enabled by shaking the remote sideways twice
- Four-level battery indicator and notification when batteries must be changed
- Notifications: "HAVE A NICE DAY" and "GOOD MORNING"
- Key in name and get personalised notifications
- Plastic parts black RAL 9005
- Factory reset
- Available in seven languages (English, Danish, Swedish, French, Korean, German, Spanish)
- 2 x AAA changeable batteries (not included)
- Delivered in a fabric bag

## Options:

- Customise front and back part in colours and with logo
- Customer logo in display
- One-click drive on favourite positions and 'simultaneous drive down' button (Impulse drive)
- Sleep timer: Set a timer to let the bed move to sleeping position
- Accessory: Stand to place the HC40 on the bed side table

## Usage:

- Compatible with LINAK Bluetooth® actuator systems
- Battery life with 2 minutes use per day: 6 months
- Approved according to FCC and IC
- Approved according to UL 962, EN 62368-1, KC and RCM
- Operation temperature: 5 to 40 °C
- Storage temperature: -10 to +50 °C

## Compatibility:


The HC40 TWIST™ Advanced is compatible with:

- TD4 Advanced
- TD5 Advanced
- CBH Advanced using BLE2LIN002
- LA18IC Advanced
- KA20IC




Do **not** expose to direct sunlight.

### Dimension drawing






**Accessory**  
**HC40STAND001**




An accessory to give the HC40 TWIST™ a base on the bed side table.  
Colour: Black RAL9005.  
Item number: HC40STAND001

**Dimension drawing**



**HC40 TWIST™ Advanced**  
**Ordering example:**



The HC40 TWIST™ Advanced comes in boxes of 79 pieces and must be ordered in quantity divisible by 79.

The 2 x AAA batteries are not included and must be ordered separately. The article number (bag with 2 x AAA batteries) is: 0063023.

The HC40 stand is an accessory and must be ordered separately. The article number is HC40STAND001.

**Terms of use**

The user is responsible for determining the suitability of LINAK products for specific application. LINAK takes great care in providing accurate and up-to-date information on its products. However, due to continuous development in order to improve its products, LINAK products are subject to frequent modifications and changes without prior notice. Therefore, LINAK cannot guarantee the correct and actual status of said information on its products. While LINAK uses its best efforts to fulfill orders, LINAK cannot, for the same reasons as mentioned above, guarantee the availability of any particular product. Therefore, LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or other written material drawn up by LINAK. All sales are subject to the Standard Terms of Sale and Delivery for LINAK. For a copy hereof, please contact LINAK.