



# Hand Control HC40 TWIST™ Standard Data sheet

# HC40 TWIST™ Standard

---

The Hand Control HC40 TWIST™ Standard for the operation of electric adjustable beds is designed to match modern bedroom interior. The HC40 TWIST™ sets a new standard within hand control design and even a basic bed system can now be created with a well-designed hand control. It is designed for a basic bed system with back and leg adjustment up/down as well as simultaneous drive.

The HC40 TWIST™ fits ergonomically well in the hands of both right-handers and left-handers. Hold it and you will experience how natural and relaxed the position of your hand is when controlling the bed. Reference lines on the back and concave and convex buttons on the front ensure one-grip-reach-all-buttons and an easy orientation of the remote.

The HC40 TWIST™ is developed for easy customisation. Customise the colour or surface and make a unique offering for a specific brand or bed series.



---

## Features:

- Unique design
- Ergonomically good to hold in the hand
- Control 2 references (Back and leg as standard)
- Simultaneous drive up and down
- Plastic parts black RAL 9005
- 2 x AAA changeable batteries (not included)
- Backlight in buttons
- Button for Under Bed Light
- Delivered in a fabric bag




## Options:

- Customise front and back part in colours and with logo
- Enable child lock
- Accessory: Stand to place the HC40 on the bed side table


## Usage:

- Compatible with the TD4 Standard, TD5 Standard and the Bluetooth® Adapter.
- Battery life at normal use of 1 minute per day is approximately 7 years
- Will be approved according to FCC and IC
- Will be approved according to UL 962, EN60335-1 and KC
- Operational temperature: 5 to 40°C
- Stock temperature: -10 to +50°C

Dimension drawing




**Accessory  
HC40STAND001**




An accessory to give the HC40 TWIST™ a base on the bed side table.  
Colour: Black RAL9005.  
Item number: HC40STAND001

**Dimension drawing**



## HC40 TWIST™ Standard

### Ordering example:



The HC40 TWIST™ Standard comes in boxes of 79 pieces and must be ordered in quantity divisible by 79.

The 2 x AAA batteries are not included and must be ordered separately. The article number (bag with 2 x AAA batteries) is: 0063023.

The HC40 stand is an accessory and must be ordered separately. The article number is HC40STAND001.

#### Terms of use

The user is responsible for determining the suitability of LINAK products for specific application. LINAK takes great care in providing accurate and up-to-date information on its products.

However, due to continuous development in order to improve its products, LINAK products are subject to frequent modifications and changes without prior notice. Therefore, LINAK cannot guarantee the correct and actual status of said information on its products.

While LINAK uses its best efforts to fulfill orders, LINAK cannot, for the same reasons as mentioned above, guarantee the availability of any particular product. Therefore, LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or other written material drawn up by LINAK.

All sales are subject to the Standard Terms of Sale and Delivery for LINAK. For a copy hereof, please contact LINAK.