



Battery BAL50 Data sheet

BAL50

The BAL50 Li-Ion battery pack is a part of the LIFT50 product series specially developed for patient lifts.

LIFT50 is a complete system consisting of the control box COL50, a battery BAL50 and an external charger CHL50 in a flexible solution. Combined with one or more actuators and a hand control, you have a complete system for modern patient lifts and sit-to-stand lifts.

The BAL50 is a next generation Li-Ion battery technology for high performance and improved return on investment (ROI) due to long lifetime. Packaged in a light, small and ergonomic package for fast and single-handed battery exchange.

The environmental footprint of lithium ion batteries is low due to less waste as only one battery is to be scrapped instead of previously 5 batteries. This also means that less transportation is necessary because of the lower battery weight which is only half the weight of lead acid batteries.



Feature highlights:

- LINAK Li-Ion battery
- Small and light-weight in an ergonomic package for fast and single-handed battery exchange.
- Readily available emergency stop – Brand new concept
- Li-Ion batteries will give you much faster return on investment (ROI)

Features and options:

- Capacity: 2.6 Ah
- Weight: 0.9 kg
- Cycles per charge (lifts/lowerings): Approx. 40 cycles*
- Charging time (approx.): 5 h
- Chemistry: NMC
- Energy: 65.52 Wh
- Voltage: 25.2 V
- IP rating: IPX6
- Colour: Signal white RAL 9003

* Number of lifts and lowerings with a fully charged battery under the following conditions:


Normal speed (COL50 and LA44), thrust up to 6,000 N
Stroke: $S = 200$ mm. The actuator does not reach the end position at any time.

Usage:

- Compatibility: COL50 and CHL50
- Duty cycle: Max. 10% (or 2 min. continuous use followed by 18 min. without use) at max. discharge current (10 A)
- Charging: Via external wall charger CHL50 or via COL50 with integrated charger
- Charging state: Maximum 30% when shipped from LINAK
- Recharging during storage: First recharge of the battery must be no later than 12 months after production date stated on the label. Hereafter the battery must be recharged at least every 12 months.
- Operating temperature: +5 °C to +40 °C
- Charging temperature: +5 °C to +40 °C
Charging at elevated temperatures can impact the charging time
- Charging time: Approx. 5 h
- Storage temperature: +10 °C to +40 °C (+10 °C to +25 °C recommended) The batteries must be stored in an applicable storage room without direct sunlight.
- Relative humidity: 20% - 80% – non-condensing
- Atmospheric pressure 700 to 1060 hPa
- Meters above sea level: Max. 3000 meters
- Approvals (pending): IEC 60601-1
ANSI/AAMI ES60601-1
CSA CAN/CSA-C22.2 NO. 60601-1
IEC 60601-2
IEC62133-2






**Ordering example
BAL50**

BA L50 D 6 B 26 0 S 000



Remark: NMC = LiNiMnCoO2 = Lithium Nickel Manganese Cobalt Oxide

Dimension drawing



Drawing no.: 1039w4000

LINAK® will remedy defective Li-Ion batteries built into LINAK products in accordance with the terms stipulated in the LINAK Li-Ion battery disclaimer available on the LINAK website. LINAK explicitly disclaims all other remedies and liability.

LINAK® accepts no responsibility for possible errors or inaccuracies in catalogues, brochures, and other material. LINAK reserves the right to change its products without prior notice. LINAK cannot guarantee product availability and reserves the right to discontinue the sale of any product. The user is responsible for determining the suitability of LINAK products for a specific application. All sales are subject to the 'Standard Terms of Sale and Delivery', available on LINAK websites.

LINAK and the LINAK logotype are registered trademarks of LINAK A/S. All rights reserved.