



CBD6S 200 W and 300 W (SMPS) Data sheet

CBD6S 200 W and 300 W (SMPS)

The DESKLINE® control box family CBD6S (SMPS) is an optimum choice for a wide range of desk applications. The CBD6S is perfect if you need a small and compact control box that requires a minimum of space when mounted. The CBD6S lifts the line of intelligent DESKLINE control boxes to a new level. While keeping the advantages from earlier generations it adds so much more. It is the most compact and lightweight control box in the DESKLINE series. It keeps the same width as DESKLINE columns with motor housings ensuring that it fits into a topframe, and it is only 38 mm high. From a design perspective, the control box is more intuitive. It has plugs for connection of the legs in each end of the box and it is equipped with cable grooves at the bottom making it easy to lead and hide motor cables from one side of the desk to the other. Furthermore, the plugs are white so they are easily recognised under the desk.

The CBD6S is available in 2 main versions, a 2-channel version (200 W) and a 2, 3 or 4-channel version with more effect (300 W). The CBD6S 300 W is a universal control box meaning that it works worldwide, just add the required mains cable. The control boxes CBD6S are compatible with the entire DESKLINE product programme of columns (DL), built-in actuators (DB) and desk panels as standard. The control box ensures smooth drive of the desk and soft start and stop of the connected columns.

Further features are autodetection of the type and number of DL/DB, making the CBD6S very intuitive to use in a desk design.

From an environmental point of view, the CBD6S is a good choice as the CBD6S has extremely low power consumption in standby mode, only 0.1 W and the CBD6S control box is PVC-Free™, which is state-of-the-art.



CBD6S 200 W features:

- The CBD6S can be connected to 1 or 2 DESKLINE® actuators / columns
- Mains voltage 230 VAC, 50 Hz, or 120 VAC, 60 Hz
- Ultra-compact; length 210 mm length
- Lightweight control box; weight only approx. 400 g

CBD6S 300 W features:

- The CBD6S can be connected to 1, 2, 3 or 4 DESKLINE® actuators / columns
- Mains voltage 100-240 VAC, 50-60 Hz (universal)
- Ultra-compact; length 265 mm length
- Lightweight control box; weight only approx. 500 g

Common features for the CBD6S (200 W and 300 W):

- Ultra-low; height only 38 mm
- Environment: Operation Storage
Ambient temperature: 5 to 40 °C -10 °C to +50 °C
Relative humidity: 20 to 80 % at 30 °C 20 to 80 % at 30 °C
Atmospheric pressure: 700 to 1060 hPa 700 to 1060 hPa
- Compact high-power SMPS (Switch Mode Power Supply)
- Colour: black
- Protection against overload (EOP), by individual current limitation

- The control box is designed with a soft start/stop function
 - Autodetection of the number and type of DL/DB connected
- Possible combinations:

CBD6S version	No. of channels	Single*	2 parallel	3 parallel	4 parallel
200 W	2	X	X		
300 W	2-4	X	X	X	X

* Single means that you plug in only one DL/DB in channel 1.

- Cable grooves at the bottom to optimise cable management
- White plugs for easy recognition when mounting/dismounting
- PVC-Free™ as standard
- Low standby power consumption – only 0.1 W.
This is what we call ZERO™
- Exchangeable standard mains cable

Options:

- Anti-Collision™. A system with Anti-Collision can limit the material damage on a desk if a collision with a solid object should occur (only for 3-stage columns)
- Compatible with the battery box BA001 (CBD6S with SW version 1.37 and later)
- CBD6S with SW version 1.37 and later is as standard equipped with multi-parallel software (only CBD6S with SW version 1.46 or later works in multi-parallel systems with DPG). All CBD6S used in a multi-parallel system must always contain the same software version.
- Compatible with Safety Limit Switch CBDSLS.


Usage:

- Duty cycle max. 10 % \approx 6 minutes per hour or 2 minutes at continuous use at full load
- The control box is compatible with all DESKLINE® columns, built-in actuators and DESKLINE controls.
- Please note the LA23, LA31, DL1A, DL2 and DL61 1200 N without PIEZO™ and BL1 require a special configuration (use the CBD6S configurator)
- Approvals and regional usage

Version	Power supply	Approvals	Region
300 W	100-240 V AC	EN 60335-1, EN 13849-1, UL 962	Worldwide
200 W	230 V AC	EN 60335-1, EN 13849-1	Europe and Australia
200 W	120 V AC	UL 962	The US
200 W	100 V AC	PSE	Japan


* BL1 in combination with CBD6S is not approved in accordance with EN 60335-1 and UL 962 and cannot lift the specified max. load. If you have any questions regarding this, please contact Technical Support.

CBD6S (200 W) dimensions:




A1/A2	Control ports for connection of one or two desk panels or the Anti-Collision™ dongle A1/A2 are parallel ports
AC	Connection to the mains supply
1 and 2	Sockets for one or two DL/DB

CBD6S (300 W) dimensions:



A1/A2	Control ports for connection of one or two desk panels or the Anti-Collision™ dongle A1/A2 are parallel ports
AC	Connection to the mains supply
1 to 4	Sockets for one to four DL/DB

CBD6S
Ordering example:



All cables for creating a fully connected DESKLINE system must be ordered separately. We offer a range of different versions and lengths. For more information such as ordering number, colour and length of the cables, please contact your local LINAK.

Terms of use

The user is responsible for determining the suitability of LINAK products for specific application. LINAK takes great care in providing accurate and up-to-date information on its products.

However, due to continuous development in order to improve its products, LINAK products are subject to frequent modifications and changes without prior notice. Therefore, LINAK cannot guarantee the correct and actual status of said information on its products.

While LINAK uses its best efforts to fulfil orders, LINAK cannot, for the same reasons as mentioned above, guarantee the availability of any particular product. Therefore, LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or other written material drawn up by LINAK.

All sales are subject to the Standard Terms of Sale and Delivery for LINAK. For a copy thereof, please contact LINAK.