

LC1 DESKLINE

Data Sheet





The LC1 DESKLINE is a three-part aluminium lifting column which is an ideal choice for adjusting the height of high-load applications that demand strength and sturdiness. The three-part construction has a short installation dimension and a long stroke length, which ensures ergonomic flexibility. The LC1 is the optimal choice for consoles, industrial workstations, work benches, assembly desks, and office desks.

The LC1 outer profile has grooves in three sides, so a mounting bracket can be used for placement of, for example, a crossbar or a customised encapsulation. For easy mounting and simple system integration, an optional end-plates kit is available.

The LC1 system is controlled by a DESKLINE® control box (CBD). The control box ensures optimal parallel drive and a pleasantly low noise level. The LC1 can be used as a single column, with 2, 3 or 4 columns in parallel systems, or with up to 16 columns in multi-parallel systems. A Desk Sensor™ 1 anti-collision dongle can be plugged into the control box to limit material damage to the application or an object in case a collision occurs during driving of the application.

Features/Accessories/Usage

Features

- Three-part lifting column
- In combination with CBD6S:

Parameter	Spindle pitch 10 mm	Spindle pitch 6 mm
Max. speed (unloaded)	30 mm/s	19 mm/s
Max. load per column	2500 N	4000 N

- Motor: 24 V DC
- Installation dimensions: 560 mm
518 mm (BIFMA)
- Stroke length: 650 mm
665 mm (BIFMA)
- Weight: Approximately 12.5 kg
- Dimensions: 140 x 175 mm (see also [Dimension drawings](#))
- Bending moment: Max. 250 Nm dynamic
- Colour: Available in natural anodised aluminium with grey top frames and zinc-grey end plates
- Prepared for mounting bracket on three sides of the column (see [Dimension drawings](#) and [Mounting bracket](#))
- Low noise level

Accessories

- Black end plates kit
- Mounting bracket
- Cable lock and self-tapping screw
- Desk Sensor™ 1 anti-collision dongle

Usage

- Single or 2, 3 or 4 parallel drive or even multi-parallel with up to 16 columns
- Duty cycle: max. 10 % \approx max. 2 minutes continuous use followed by 18 minutes pause
- For indoor use in dry locations

Parameter	Operation	Storage and transportation
Temperature	10 to 40 °C	-10 to +50 °C
Relative humidity	20% to 80% - non-condensing	20% to 80% - non-condensing
Atmospheric pressure	700 to 1060 hPa	700 to 1060 hPa
Altitude	Max. 2000 m	Max. 2000 m

- System compliance, see the Declaration of Conformity in the [User Manual](#)
- Compatible and UL-approved with DESKLINE® control boxes (must be configured)
- Compatible with all DESKLINE® controls

Ordering

	LC1	
SPINDLE PITCH	100	060 = 6 mm (max. 4000 N) 100 = 10 mm (max. 2500 N)
STROKE LENGTH	650	650 = 650 mm 665 = 665 mm (BIFMA)
OPTION	T000	T000 = Standard
POSITIONING	1H	1H = Hall sensor
OUTER PROFILE	C	C = Standard DESKLINE (Outer profile prepared with dovetail grooves)
INSTALLATION DIMENSION	0560	0560 = 560 mm 0518 = 518 mm (BIFMA)
OPTION	0	0 = None
MOTOR TYPE	G	G = Standard DESKLINE motor
END STOP	0	0 = Power switch
IP DEGREE	6	6 = IPX6
CLOUR	+	+ = Aluminium
END PLATE OPTIONS	E	E = Standard end plate for DESKLINE profiles
OPTION	0000	0000 = Standard

Selected item type **LC1100650T0001HC05600G06+E0000**



For use with CBD6S, remember to order the adaptor cable CAB0964764 for the LC1.



All cables for creating a fully connected DESKLINE® system must be ordered separately. We offer a range of different versions and lengths. For information such as ordering number, colour and cable lengths, please contact your local LINAK.

Accessories

Kits

Remember to order cable-lock, mounting-plate, and mounting-bracket kits separately:

Article number	Contents	Purpose	Order quantities
1053W8011	1 x Mini-Fit cable lock 1 x self-tapping screw, Ø4 x 10 mm	Securing the adaptor cable	Boxes of 100 pieces
1053W8012	1 x top end plate (14 mm) 1 x bottom end plate (10 mm) 8 x screw, Ø8 x 40 mm	Mounting the top and bottom end plates Torque: 20 Nm ± 10 %	Packed individually - no minimum quantity
0578006	1 x mounting bracket 2 x screws, M8 x 12 mm	Mounting a bracket in the groove	Boxes of 60 pieces

Mounting screws

It is possible to use the customers' own top and bottom end plates.

Please note: The screws must go minimum 30 mm into the LC1 column.

For mounting customised top and bottom end plates, two LINAK mounting screws are available:

Article number	Description
0002445	Ø8 x 40 mm, self-tapping screw, EJOT PT
0002085	Ø8 x 60 mm, self-tapping screw, EJOT PT

Dimension drawings

LC1 DESKLINE





Figure 1 LC1 without end plates dimensions (mm)



Version	L [mm]
EU	584
BIFMA	542

Figure 2 LC1 dimensions with 14 mm top end plate and 10 mm bottom end plate (mm)

End plates



All measurements are without powder coating.




Figure 3 Top end plate dimensions (mm)




Figure 4 Bottom end plate dimensions (mm)




A customised top end plate must cover the entire top plate of LC1 and be strong enough to carry the load.

Mounting bracket

The mounting bracket can for example be used for placement of a crossbar, a customised cover for encapsulation, a control box, or a computer.

The mounting bracket order code is: 0578006.



Contacts

FACTORIES

Denmark - Headquarters
LINAK A/S
Phone: +45 73 15 15 15
Fax: +45 74 45 80 48
Fax (Sales): +45 73 15 16 13
Web: www.linak.com

China
LINAK (Shenzhen) Actuator Systems, Ltd.
Phone: +86 755 8610 6656
Fax: +86 755 8610 6990
Web: www.linak.cn

Slovakia
LINAK Slovakia s.r.o.
Phone: +421 51 7563 444
Web: www.linak.sk

Thailand
LINAK APAC Ltd.
Phone: +66 33 265 400
Web: www.linak.com

USA
LINAK U.S. Inc.
Americas Headquarters
Phone: +1 502 253 5595
Fax: +1 502 253 5596
Web: www.linak-us.com
www.linak-latinamerica.com

SUBSIDIARIES

Australia
LINAK Australia Pty. Ltd
Phone: +61 3 8796 9777
Fax: +61 3 8796 9778
E-mail: sales@linak.com.au
Web: www.linak.com.au

Austria
LINAK Zweigniederlassung - Österreich (Wien)
Phone: +43 (1) 890 7446
Fax: +43 (1) 890 744615
E-mail: info@linak.de
Web: www.linak.at - www.linak.hu

Belgium
LINAK Actuator-Systems NV/SA
(Belgium & Luxembourg)
Phone: +32 (0)9 230 01 09
E-mail: beinfo@linak.be
Web: www.linak.be - www.fr.linak.be

Brazil
LINAK Do Brasil Comércio De Atuadores Ltda.
Phone: +55 (11) 2832 7070
Fax: +55 (11) 2832 7060
E-mail: info@linak.com.br
Web: www.linak.com.br

Canada
LINAK Canada Inc.
Phone: +1 502 253 5595
Fax: +1 416 255 7720
E-mail: info@linak.ca
Web: www.linak-us.com

Czech Republic
LINAK C&S s.r.o.
Phone: +42 058 174 1814
Fax: +42 058 170 2452
E-mail: info@linak.cz
Web: www.linak.cz - www.linak.sk

Denmark - International
LINAK International
Phone: +45 73 15 15 15
E-mail: info@linak.com
Web: www.linak.com

Denmark - Sales
LINAK Danmark A/S
Phone: +45 86 80 36 11
Fax: +45 86 82 90 51
E-mail: linak@linak-silkeborg.dk
Web: www.linak.dk

Finland
LINAK OY
Phone: +358 10 841 8700
E-mail: linak@linak.fi
Web: www.linak.fi

France
LINAK France E.U.R.L.
Phone: +33 (0) 2 41 36 34 34
Fax: +33 (0) 2 41 36 35 00
E-mail: linak@linak.fr
Web: www.linak.fr

Germany
LINAK GmbH
Phone: +49 6043 9655 0
Fax: +49 6043 9655 60
E-mail: info@linak.de
Web: www.linak.de

India
LINAK A/S India Liaison Office
Phone: +91 120 4531797
Fax: +91 120 4786428
E-mail: info@linak.in
Web: www.linak.in

Ireland
LINAK UK Limited (Ireland)
Phone: +44 (0)121 544 2211
Fax: +44 (0)121 544 2552
+44 (0)796 855 1606 (UK Mobile)
+35 387 634 6554 (Rep.of Ireland Mobile)
E-mail: sales@linak.co.uk
Web: www.linak.co.uk

Italy
LINAK ITALIA S.r.l.
Phone: +39 02 48 46 33 66
Fax: +39 02 48 46 82 52
E-mail: info@linak.it
Web: www.linak.it

Japan
LINAK K.K.
Phone: 81-45-533-0802
Fax: 81-45-533-0803
E-mail: linak@linak.jp
Web: www.linak.jp

Malaysia
LINAK Actuators Sdn. Bhd.
Phone: +60 4 210 6500
Fax: +60 4 226 8901
E-mail: info@linak-asia.com
Web: www.linak.my

Netherlands
LINAK Actuator-Systems B.V.
Phone: +31 76 5 42 44 40 /
+31 76 200 11 10
E-mail: info@linak.nl
Web: www.linak.nl

New Zealand
LINAK New Zealand Ltd
Phone: +64 9580 2071
Fax: +64 9580 2072
E-mail: nzsales@linak.com.au
Web: www.linak.com.au

Norway
LINAK Norge AS
Phone: +47 32 82 90 90
E-mail: info@linak.no
Web: www.linak.no

Poland
LINAK Polska
LINAK Danmark A/S (Spółka Akcyjna)
Phone: +48 22 295 09 70 /
+48 22 295 09 71
E-mail: info@linak.pl
Web: www.linak.pl

Republic of Korea
LINAK Korea Ltd.
Phone: +82 2 6231 1515
Fax: +82 2 6231 1516
E-mail: info@linak.kr
Web: www.linak.kr

Slovakia
LINAK Slovakia S.R.O.
Phone: +421 51 7563 444
Web: www.linak.sk

Spain
LINAK Actuadores, S.L.U
Phone: +34 93 588 27 77
Fax: +34 93 588 27 85
E-mail: esma@linak.es
Web: www.linak.es

Sweden
LINAK Scandinavia AB
Phone: +46 8 732 20 00
Fax: +46 8 732 20 50
E-mail: info@linak.se
Web: www.linak.se

Switzerland
LINAK AG
Phone: +41 43 388 31 88
Fax: +41 43 388 31 87
E-mail: info@linak.ch
Web: www.linak.ch - www.fr.linak.ch
www.it.linak.ch

Taiwan
LINAK (Shenzhen) Actuator systems Ltd.
Taiwan Representative office
Phone: +886 2 272 90068
Fax: +886 2 272 90096
E-mail: sales@linak.com.tw
Web: www.linak.com.tw

Turkey
LINAK İth. İhr. San. ve Tic. A.Ş.
Phone: +90 312 4726338
Fax: +90 312 4726635
E-mail: info@linak.com.tr
Web: www.linak.com.tr

United Kingdom
LINAK UK Limited
Phone: +44 (0)121 544 2211
Fax: +44 (0)121 544 2552
E-mail: sales@linak.co.uk
Web: www.linak.co.uk

Argentina
Novotec Argentina SRL
Phone: 011-4303-8989 / 8900
Fax: 011-4032-0184
E-mail: info@novotecargentina.com
Web: www.novotecargentina.com

Colombia
MEM Ltda
Phone: +57 (1) 334-7666
Fax: +57 (1) 282-1684
E-mail: servicioalcliente@memltda.com.co
Web: www.mem.net.co

India
Mechatronics Control Equipments India Pvt Ltd
Phone: +91-44-28558484, 85
E-mail: bala@mechatronicscontrol.com
Web: www.mechatronicscontrol.com

Indonesia
PT. Himalaya Everest Jaya
Phone: +6 221 544 8956 /+6 221 544 8965
Fax: +6 221 619 1925
Fax (Sales): +6 221 619 4658
E-mail: hejplastic-div@centrin.net.id
Web: www.hej.co.id

Israel
NetivTech LTD
Phone: +972 55-2266-535
Fax: +972 2-9900-560
Email: info@NetivTech.com
Web: www.netivtech.com

Singapore
Servo Dynamics Pte Ltd
Phone: +65 6844 0288
Fax: +65 6844 0070
E-mail: servodynamics@servo.com.sg

South Africa
Industrial Specialised Applications CC
Phone: +27 011 466 0346
E-mail: gartht@isagroup.co.za
Web: www.isaza.co.za

United Arab Emirates
Mechatronics
Phone: +971 4 267 4311
Fax: +971 4 267 4312
E-mail: mechtron@emirates.net.ae

DISTRIBUTORS

Terms of use

LINAK® takes great care in providing accurate and up-to-date information on its products. However, the user is responsible for determining the suitability of LINAK products for a specific application. Due to continual development, LINAK products are subject to frequent modifications and changes. LINAK reserves the rights to conduct modifications, updates, and changes without any prior notice. For the same reason, LINAK cannot guarantee the correctness and actual status of imprinted information on its products.

LINAK uses its best efforts to fulfil orders. However, for the reasons mentioned above, LINAK cannot guarantee availability of any particular product at any given time. LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or in other written material created and produced by LINAK, LINAK subsidiaries, or LINAK affiliates. All sales are subject to the 'Standard Terms of Sale and Delivery for LINAK A/S' available on LINAK websites. LINAK and the LINAK logotype are registered trademarks of LINAK A/S. All rights reserved.



WE IMPROVE YOUR LIFE