


Linear Actuator LA23

Data Sheet



Contents

Introduction.....	3
Features and options	4
Usage	5
Ordering example	7
Positioning options.....	8
Dimensions	10
Built-in dimensions	11
Self-locking specifications	12
Technical specifications.....	13
Safety nut and back fixture overview.....	13

Introduction



The LA23 is a small and strong push/pull actuator (up to 2,500 N). The LA23 can be used in various applications where size is important.

Some of the benefits the LA23 offers you are:

- Compact design
- High lifting force
- Exchangeable cables
- IPX6 Washable DURA™

The standard LA23 is available for the CARELINE®, MEDLINE®, TECHLINE® product ranges.

Features and options

Load in push:	2,500 N, 1,800 N, 1,500 N, 1,200 N, 900 N or 300 N
Load in pull:	2,500 N, 1,800 N, 1,500 N, 1,200 N, 900 N or 300 N
Dynamic push and pull:	Actuators are designed for push or pull applications. If a combination is required, please contact your local LINAK salesperson.
Housing colour:	Black (RAL 9005), outer tube steel or black Light grey (RAL 7035), outer tube steel
Protection class:	IPX4, IPX6, IPX6 Washable DURA™
Motor:	12 V DC, 24 V DC
Stroke length:	20 - 500 mm (for stroke 300-500 mm max. load is 1,000 N for pitch 3, 5, 6 and 9) Pitch 12 mm (for stroke 300-500 mm max. load is 900 N) Pitch 20 mm (for stroke 300-500 mm max. load is 300 N)
Built-in dimensions:	110 - 146 mm + stroke length
Positioning options:	Potential free end stop signals Hall potentiometer or Hall PWM position Single Hall, Dual Hall
Back fixture material:	Plastic or steel
Nut:	Guided
Safety nut:	In push or pull (2,500 N and 1,800 N version only safety nut in push)
Mechanical spline:	Yes
Built-in electrical end stop:	Yes
Exchangeable cable:	Yes
Static safety factor:	2.5
Noise level:	Max. 58.5 dB(A) (At nominal voltage and with no load, according to EN ISO 3743-1)
Mechanical end stop:	Yes
Integrated control:	Yes



Usage

Duty cycle:	10%, 2 minutes continuous use followed by 18 minutes not in use
Operation temperature:	+5° - +40° normal operating temp. -30° - +50° according to test conditions: ISO 7176-9
Storage temperature:	-45 °C to +70 °C (according to ISO 7176-9)
Compatibility:	Compatible with LINAK control boxes. Please contact LINAK.
Relative humidity:	20% to 80% – non-condensing
Atmospheric pressure:	700 to 1060 hPa
Meters above sea level:	Max. 3000 meters
Flammability rating:	Enclosure UL94-V0
Approvals:	IEC60601-1 ANSI/AAMI ES60601-1 CAN/CSA-22.2 No 60601-1
Cycles:	The LA23 Life cycle test has been performed with a stabilised power supply (10% duty cycle) on a 200mm stroke actuator at max. load for the following number of cycles (at 20 °C ambient temperature): 3 mm pitch = 5000 cycles 5, 6, 9, 12 and 20 mm pitch = 10,000 cycles



LA23 is always equipped with mechanical end stop - to ensure first failure safety.

In the norm, EN 60601-1, it is mentioned that an application must be first failure safe. If the electrical end stop in the LA23 should fail, the built-in mechanical end stop ensures that the LA23 cannot run out of the spindle.

The mechanical end stop is only being used as a safety backup for the electrical end stop.

If electrical end stop fails to function, the actuator will continue to retract or extend until mechanical end stop is reached.

The customer application must be able to obtain or withstand an actuator with failing electrical end stop.

For actuators with stroke length (SL) < 50 mm:

Typical minimum length of actuator reaching mechanical end stop: BID - 2 mm.

Typical maximum length of actuator reaching mechanical end stop: BID + SL + 52 mm.

For actuators with stroke length (SL) ≥ 50 mm:

Typical minimum length of actuator reaching mechanical end stop: BID - 2 mm.

Typical maximum length of actuator reaching mechanical end stop: BID + SL + 4 mm.



Ordering example

<p>23 0 1 0 0 1 0 0 0 2 5 0 B 4</p>	<p>HOUSING/IP DEGREE:</p> <p>MOTOR TYPE:</p> <p>STROKE:</p> <p>POSITIONING:</p> <p>SAFETY OPTION:</p> <p>HOUSING COLOUR:</p> <p>PISTON ROD EYE:</p> <p>BACK FIXTURE ROTATION:</p> <p>BACK FIXTURE:</p> <p>SPINDLE TYPE:</p> <p>ACTUATOR TYPE:</p>	<p>4=IPX4 6=IPX6 W=IPX6 Washable DURA</p> <p>A = 12 V B = 24 V (driving mainly with battery (CBJ1, CBJ2, CBJH, CBJC, wheelchairs)) G = 24 V (33 V) (For OpenBus (CB20, CB16, CB6s))</p> <p>XXX = mm Min. 020 mm In steps of 5 mm Max. 300 mm</p> <p>(For minimum BID see table 2)</p> <p>XX = See table 1</p> <p>0 = No safety option 1 = Safety nut for push 2 = Safety nut for pull 3 = Spline without safety nut 4 = Spline + safety nut push</p> <p>1 = Black (RAL 9005) + grey outer tube 2 = Light grey (RAL7035) + grey outer tube 3 = Black (RAL 9005) + black outer tube</p> <p>0 = Standard steel with slot (6.1 mm), eye Ø10.1 mm, incl. plastic bushings 1 = Standard steel with slot (6.1 mm), eye Ø10.1 mm 2 = Standard steel with slot (6.1 mm), eye Ø12.3 mm</p> <p>0 = 0° clockwise 1 = 90° clockwise A = 7.5° clockwise M = 97.5° clockwise B = 15° clockwise N = 105° clockwise C = 22.5° clockwise P = 112.5° clockwise D = 30° clockwise Q = 120° clockwise E = 37.5° clockwise R = 127.5° clockwise F = 45° clockwise S = 135° clockwise G = 52.5° clockwise T = 142.5° clockwise H = 60° clockwise U = 150° clockwise J = 67.5° clockwise V = 157.5° clockwise K = 75° clockwise W = 165° clockwise L = 82.5° clockwise Z = 172.5° clockwise</p> <p>1 = Plastic with slot (6.1 mm), eye Ø10.1, (only for standard push load) 2 = Steel with slot (6.1 mm), eye Ø10.1 mm, incl. plastic bushings 3 = Steel with slot (6.1mm), eye Ø10.1 mm 4 = Steel with slot (6.1mm), eye Ø12.3 mm</p> <p>0 = 12 mm pitch (900 N) 2 = 20 mm pitch (300 N) 3 = 3 mm pitch (2500 N) 5 = 5 mm pitch (1800 N) 6 = 6 mm pitch (1500 N) 9 = 9 mm pitch (1200 N)</p> <p>23 = LA23</p>
-------------------------------------	---	--



Positioning options

Table1

Different positioning options can be chosen for LA23.



Positioning/ Ordering code number		Description of positioning option		No. of pins in LA23
X	X			
0	0	Standard electrical endstop - no positioning		6
0	1	Standard electrical endstop and potential free endstop - no positioning		6
0	2	Dual Hall digital positioning		6
0	3	Dual Hall PNP positioning		6
0	4	Dual Hall, encoded		6
1	1	Hall Potentiometer feedback	0-10V	10
1	2	Hall Potentiometer feedback	1-9V	10
1	3	Hall Potentiometer feedback	2-8V	10
1	4	Hall Potentiometer feedback	0-5V	10
1	5	Hall Potentiometer feedback	0.5-4.5V	10
1	6	Hall Potentiometer feedback	0-3.3V	10
1	7	Hall Potentiometer feedback	0.3-3V	10
2	1	Hall Potentiometer feedback and potential free endstop	0-10V	10
2	2	Hall Potentiometer feedback and potential free endstop	1-9V	10
2	3	Hall Potentiometer feedback and potential free endstop	2-8V	10
2	4	Hall Potentiometer feedback and potential free endstop	0-5V	10
2	5	Hall Potentiometer feedback and potential free endstop	0.5-4.5V	10
2	6	Hall Potentiometer feedback and potential free endstop	0-3.3V	10
2	7	Hall Potentiometer feedback and potential free endstop	0.3-3V	10
3	1	Hall PWM position feedback	0-100%	10
3	2	Hall PWM position feedback	10-90%	10
3	3	Hall PWM position feedback	20-80%	10
4	1	Hall PWM position feedback and with potential free endstop	0-100%	10
4	2	Hall PWM position feedback and with potential free endstop	10-90%	10
4	3	Hall PWM position feedback and with potential free endstop	20-80%	10





Positioning/ Ordering code number X X		Description of positioning option IC (Integrated Control)		No. of pins in LA23
5	0	Standard electrical endstop - no positioning		10
5	2	Standard single Hall positioning		10
6	1	Hall potentiometer feedback	0 - 10V	10
6	2	Hall potentiometer feedback	1 - 9V	10
6	3	Hall potentiometer feedback	2 - 8V	10
6	4	Hall potentiometer feedback	0 - 5V	10
6	5	Hall potentiometer feedback	0.5 - 4.5V	10
6	6	Hall potentiometer feedback	0 - 3.3V	10
6	7	Hall potentiometer feedback	0.3 - 3V	10
7	1	Hall PWM position feedback	0-100%	10
7	2	Hall PWM position feedback	10-90%	10
7	3	Hall PWM position feedback	20-80%	10



Dimensions




Back fixture orientation
Option 1



Back fixture orientation
Option 0

Example A

See explanation page 12.



Drawing no.: 0234024

Tolerances

For built-in dimensions and stroke ± 2 mm.



Built-in dimensions

Table 2

The built-in dimension depends upon the chosen safety option and stroke length.

Please see the table below to decide upon the built-in dimension.

Safety option	Stroke length	Spindle pitch	Min. built-in Dimensions
0 = No safety option	20 - 49	6, 9, 12 or 20	160
0 = No safety option	20 - 49	3, 5	168
1 = Safety nut for push	20 - 49	6, 9 or 12	160
1 = Safety nut for push	20 - 49	3, 5	168
2 = safety nut for pull	20 - 49	6, 9 or 12	172
3 = Mechanical Spline for push	20 - 49	6, 9 or 12	180
3 = Mechanical Spline for push	20 - 49	3, 5	196
4 = Mechanical Spline & safety nut for push	20 - 49	6, 9 or 12	180
4 = Mechanical Spline & safety nut for push	20 - 49	3, 5	196
0 = No safety option	50 - 200	6, 9, 12 or 20	110 + stroke
0 = No safety option	50 - 200	3, 5	118 + stroke
1 = Safety nut for push	50 - 200	6, 9 or 12	110 + stroke
1 = Safety nut for push	50 - 200	3, 5	118 + stroke
2 = Safety nut for pull	50 - 200	6, 9 or 12	122 + stroke
3 = Mechanical Spline for push	50 - 200	6, 9 or 12	130 + stroke
3 = Mechanical Spline for push	50 - 200	3, 5	146 + stroke
4 = Mechanical Spline & safety nut for push	50 - 200	6, 9 or 12	130 + stroke
4 = Mechanical Spline & safety nut for push	50 - 200	3, 5	146 + stroke
0 = No safety option	201 - 500	6, 9, 12 or 20	130 + stroke
0 = No safety option	201 - 500	3, 5	138 + stroke
1 = Safety nut for push	201 - 500	6, 9 or 12	130 + stroke
1 = Safety nut for push	201 - 500	3, 5	138 + stroke
2 = Safety nut for pull	201 - 500	6, 9 or 12	142 + stroke
3 = Mechanical Spline for push	201 - 500	6, 9 or 12	150 + stroke
3 = Mechanical Spline for push	201 - 500	3, 5	166 + stroke
4 = Mechanical Spline & safety nut for push	201 - 500	6, 9 or 12	150 + stroke
4 = Mechanical Spline & safety nut for push	201 - 500	3, 5	166 + stroke



It is possible to order LA23 with extended built-in dimensions if the following requirements are fulfilled (see example "A" earlier page):

	Spindle pitch = 6, 9, 12, 20	Spindle pitch = 3, 5	Spindle pitch = 6, 9,12	Spindle pitch = 6, 9, 12	Spindle pitch = 3, 5
	Safety option 0: No safety option		Safety option 2: Safety nut pull	Safety option 3: Spline without safety nut	
	Safety option 1: safety nut push			Safety option 4: Spline + safety nut push	
Max.built-in dimensions	≤730 - stroke	≤738 - stroke	≤742 - stroke	≤750 - stroke	≤766 - stroke

Example:

- A) 6 mm pitch no safety option, stroke 200, BID can be max. $(730 - 200) = 530$
(see earlier page for further explanation)
- B) 3 mm pitch no safety option, stroke 20, BID can be max. $(738 - 20) = 718$

Self-locking specifications

Spindle Pitch	Without short circuit	With short circuit
20 mm pitch	100	300
12 mm pitch	750	900
9 mm pitch	750	1,200
6 mm pitch	1,200	1,500
5 mm pitch	1,600	1,800
3 mm pitch	2,500	2,500



Technical specifications

Power supply	Spindle pitch (mm)	Load max.** Push/Pull (N)	Motor type	*Typical speed at 0/full load (mm/sec.)	*Typical current at 0/ full load (Amp.)	Inrush current (Amp.)
12VDC	3	2,500/2,500	A: 12V	3.1 / 2.5	0.8 / 3.6	13.4
CBJ1/2, CBJH and CBJC	3	2,500/2,500	B: 24V	3.2 / 2.6	0.4 / 1.9	8.7
OpenBus™	3	2,500/2,500	G: 24V	3.3 / 2.7	0.3 / 1.4	6.2
12VDC	5	1,800/1,800	A:12V	5.4 / 4.2	0.8 / 3.9	13.4
CBJ1/2, CBJH and CBJC	5	1,800/1,800	B:24V	5.4 / 4.5	0.4 / 1.9	8.7
OpenBus™	5	1,800/1,800	G:24V	5.6 / 4.6	0.3 / 1.4	6.2
12VDC	6	1,500/1,500	A: 12V	6.6 / 5.2	0.8 / 3.6	13.4
CBJ1/2, CBJH and CBJC	6	1,500/1,500	B: 24V	6.4 / 5.5	0.4 / 1.7	8.7
OpenBus™	6	1,500/1,500	G: 24V	6.7 / 5.5	0.3 / 1.3	6.2
12VDC	9	1,200/1,200	A: 12V	9.9 / 7.5	0.9 / 4.0	13.4
CBJ1/2, CBJH and CBJC	9	1,200/1,200	B: 24V	9.5 / 8.1	0.4 / 1.9	8.7
OpenBus™	9	1,200/ 1,200	G: 24V	9.9 / 8.1	0.3 / 1.3	6.2
12VDC	12	900/900	A:12V	13 / 9.6	0.9 / 3.8	13.4
CBJ1/2, CBJH and CBJC	12	900/900	B:24V	12.6 / 10.4	0.4 / 1.9	8.7
OpenBus™	12	900/900	G:24V	13.3 / 10.7	0.3 / 1.4	6.2
12VDC	20	300/300	A:12V	21.5 / 18.6	0.8 / 4.3	–
CBJ1/2, CBJH and CBJC	20	300/300	B:24V	21.6 / 20.2	0.4 / 2.3	–
OpenBus™	20	300/300	G:24V	21.8 / 20.6	0.3 / 1.6	–

* Typical values, measurements are made with an actuator in connection with a stable power supply. The typical values can have a variation of $\pm 20\%$ on the current values and $\pm 10\%$ on the speed values.

** If the stroke is between 300-500 mm, the max. load is 1,000 N for pitch 3, 5, 6 and 9.

Safety nut and back fixture overview

Pitch (mm)	Load (N)	Safety nut	Steel back fixture	Plastic back fixture
20	300	Not an option	Required in pull	Only in push
12	900	Optional in push or pull	Required in pull	Only in push
9	1,200	Optional in push or pull	Required in pull	Only in push
6	1,500	Optional in push or pull	Required in pull	Only in push
5	1,800	Optional in push (Safety nut 1,800 N not available in pull)	Always required	Not available
3	2,500	Optional in push (Safety nut 2,500 N not available in pull)	Always required	Not available



Contacts

FACTORIES

Denmark - Headquarters
 LINAK A/S
 Phone: +45 73 15 15 15
 Fax: +45 74 45 80 48
 Fax (Sales): +45 73 15 16 13
 Web: www.linak.com

China
 LINAK (Shenzhen) Actuator Systems, Ltd.
 Phone: +86 755 8610 6656
 Phone: +86 755 8610 6990
 Web: www.linak.cn

Slovakia
 LINAK Slovakia s.r.o.
 Phone: +421 51 7563 444
 Web: www.linak.sk

Thailand
 LINAK APAC Ltd.
 Phone: +66 33 265 400
 Web: www.linak.com

USA
 LINAK U.S. Inc.
 Americas Headquarters
 Phone: +1 502 253 5595
 Fax: +1 502 253 5596
 Web: www.linak-us.com
 www.linak-latinamerica.com

SUBSIDIARIES

Australia
 LINAK Australia Pty. Ltd
 Phone: +61 3 8796 9777
 Fax: +61 3 8796 9778
 E-mail: sales@linak.com.au
 Web: www.linak.com.au

Austria
 LINAK Zweigniederlassung - Österreich (Wien)
 Phone: +43 (1) 890 7446
 Fax: +43 (1) 890 744615
 E-mail: info@linak.de
 Web: www.linak.at - www.linak.hu

Belgium
 LINAK Actuator-Systems NV/SA
 (Belgium & Luxembourg)
 Phone: +32 (0)9 230 01 09
 E-mail: beinfo@linak.be
 Web: www.linak.be - www.fr.linak.be

Brazil
 LINAK Do Brasil Comércio De Atuadores Ltda.
 Phone: +55 (11) 2832 7070
 Fax: +55 (11) 2832 7060
 E-mail: info@linak.com.br
 Web: www.linak.com.br

Canada
 LINAK Canada Inc.
 Phone: +1 502 253 5595
 Fax: +1 416 255 7720
 E-mail: info@linak.ca
 Web: www.linak-us.com

Czech Republic
 LINAK C&S s.r.o.
 Phone: +42 058 174 1814
 Fax: +42 058 170 2452
 E-mail: info@linak.cz
 Web: www.linak.cz - www.linak.sk

Denmark - International
 LINAK International
 Phone: +45 73 15 15 15
 E-mail: info@linak.com
 Web: www.linak.com

Denmark - Sales
 LINAK Danmark A/S
 Phone: +45 86 80 36 11
 Fax: +45 86 82 90 51
 E-mail: linak@linak-silkeborg.dk
 Web: www.linak.dk

Finland
 LINAK OY
 Phone: +358 10 841 8700
 E-mail: linak@linak.fi
 Web: www.linak.fi

France
 LINAK France E.U.R.L
 Phone: +33 (0) 2 41 36 34 34
 Fax: +33 (0) 2 41 36 35 00
 E-mail: linak@linak.fr
 Web: www.linak.fr

Germany
 LINAK GmbH
 Phone: +49 6043 9655 0
 Fax: +49 6043 9655 60
 E-mail: info@linak.de
 Web: www.linak.de

India
 LINAK A/S India Liaison Office
 Phone: +91 120 4531797
 Fax: +91 120 4786428
 E-mail: info@linak.in
 Web: www.linak.in

Ireland
 LINAK UK Limited (Ireland)
 Phone: +44 (0)121 544 2211
 Fax: +44 (0)121 544 2552
 +44 (0)796 855 1606 (UK Mobile)
 +35 387 634 6554 (Rep.of Ireland Mobile)
 E-mail: sales@linak.co.uk
 Web: www.linak.co.uk

Italy
 LINAK ITALIA S.r.l.
 Phone: +39 02 48 46 33 66
 Fax: +39 02 48 46 82 52
 E-mail: info@linak.it
 Web: www.linak.it

Japan
 LINAK K.K.
 Phone: 81-45-533-0802
 Fax: 81-45-533-0803
 E-mail: linak@linak.jp
 Web: www.linak.jp

Malaysia
 LINAK Actuators Sdn. Bhd.
 Phone: +60 4 210 6500
 Fax: +60 4 226 8901
 E-mail: info@linak-asia.com
 Web: www.linak.my

Netherlands
 LINAK Actuator-Systems B.V.
 Phone: +31 76 5 42 44 40 /
 +31 76 200 11 10
 E-mail: info@linak.nl
 Web: www.linak.nl

New Zealand
 LINAK New Zealand Ltd
 Phone: +64 9580 2071
 Fax: +64 9580 2072
 E-mail: nzsales@linak.com.au
 Web: www.linak.com.au

Norway
 LINAK Norge AS
 Phone: +47 32 82 90 90
 E-mail: info@linak.no
 Web: www.linak.no

Poland
 LINAK Polska
 LINAK Danmark A/S (Spółka Akcyjna)
 Phone: +48 22 295 09 70 /
 +48 22 295 09 71
 E-mail: info@linak.pl
 Web: www.linak.pl

Republic of Korea
 LINAK Korea Ltd.
 Phone: +82 2 6231 1515
 Fax: +82 2 6231 1516
 E-mail: info@linak.kr
 Web: www.linak.kr

Slovakia
 LINAK Slovakia S.R.O.
 Phone: +421 51 7563 444
 Web: www.linak.sk

Spain
 LINAK Actuadores, S.L.u
 Phone: +34 93 588 27 77
 Fax: +34 93 588 27 85
 E-mail: esma@linak.es
 Web: www.linak.es

Sweden
 LINAK Scandinavia AB
 Phone: +46 8 732 20 00
 Fax: +46 8 732 20 50
 E-mail: info@linak.se
 Web: www.linak.se

Switzerland
 LINAK AG
 Phone: +41 43 388 31 88
 Fax: +41 43 388 31 87
 E-mail: info@linak.ch
 Web: www.linak.ch - www.fr.linak.ch
 www.it.linak.ch

Taiwan
 LINAK (Shenzhen) Actuator systems Ltd.
 Taiwan Representative office
 Phone: +886 2 272 90068
 Fax: +886 2 272 90096
 E-mail: sales@linak.com.tw
 Web: www.linak.com.tw

Turkey
 LINAK İth. İhr. San. ve Tic. A.Ş.
 Phone: +90 312 4726338
 Fax: +90 312 4726635
 E-mail: info@linak.com.tr
 Web: www.linak.com.tr

United Kingdom
 LINAK UK Limited
 Phone: +44 (0)121 544 2211
 Fax: +44 (0)121 544 2552
 E-mail: sales@linak.co.uk
 Web: www.linak.co.uk

DISTRIBUTORS

Argentina
 Novotec Argentina SRL
 Phone: 011-4303-8989 / 8900
 Fax: 011-4032-0184
 E-mail: info@novotecargentina.com
 Web: www.novotecargentina.com

Colombia
 MEM Ltda
 Phone: +[57] (1) 334-7666
 Fax: +[57] (1) 282-1684
 E-mail: servicioalcliente@memltda.com.co
 Web: www.mem.net.co

India
 Mechatronics Control Equipments India Pvt Ltd
 Phone: +91-44-28558484, 85
 E-mail: bala@mechatronicscontrol.com
 Web: www.mechatronicscontrol.com

Indonesia
 PT. Himalaya Everest Jaya
 Phone: +6 221 544 8956 /+6 221 544 8965
 Fax: +6 221 619 1925
 Fax (Sales): +6 221 619 4658
 E-mail: hejplastic-div@centrin.net.id
 Web: www.hej.co.id

Israel
 NetivTech LTD
 Phone: +972 55-2266-535
 Fax: +972 2-9900-560
 Email: info@NetivTech.com
 Web: www.netivtech.com

Singapore
 Servo Dynamics Pte Ltd
 Phone: +65 6844 0288
 Fax: +65 6844 0070
 E-mail: servodynamics@servo.com.sg

South Africa
 Industrial Specialised Applications CC
 Phone: +27 011 466 0346
 E-mail: gartht@isagroup.co.za
 Web: www.isaza.co.za

United Arab Emirates
 Mechatronics
 Phone: +971 4 267 4311
 Fax: +971 4 267 4312
 E-mail: mechtron@emirates.net.ae

Terms of use

LINAK® takes great care in providing accurate and up-to-date information on its products. However, the user is responsible for determining the suitability of LINAK products for a specific application. Due to continual development, LINAK products are subject to frequent modifications and changes. LINAK reserves the rights to conduct modifications, updates, and changes without any prior notice. For the same reason, LINAK cannot guarantee the correctness and actual status of imprinted information on its products.

LINAK uses its best efforts to fulfil orders. However, for the reasons mentioned above, LINAK cannot guarantee availability of any particular product at any given time. LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or in other written material created and produced by LINAK, LINAK subsidiaries, or LINAK affiliates. All sales are subject to the 'Standard Terms of Sale and Delivery for LINAK A/S' available on LINAK websites. LINAK and the LINAK logotype are registered trademarks of LINAK A/S. All rights reserved.